
CA-SNSPD-001 Superconducting Nanowire Single Photon Detector Module

Overview

CA OPTRONICS GROUP INC's single-photon detectors module based on superconducting nanowires single photon detector (SNSPDs) have rapidly emerged as a highly promising photon counting technology for infrared wavelengths. These devices offer high efficiency, low dark counts and excellent timing resolution. In this datasheet, we consider the basic SNSPD operating principle and models of device behaviour. We give an overview of the evolution of SNSPD device design and the improvements in performance which have been achieved. We also evaluate device limitations and noise mechanisms. We survey practical refrigeration technologies and optical coupling schemes for SNSPDs. In the datasheet we also summarise promising application areas, ranging from quantum cryptography to remote sensing.





The Basic Operation Principle

The basic operation principle of the superconducting nanowire single-photon detector (SNSPD)

(a) A schematic illustrating the detection cycle.

(i) The superconducting nanowire maintained well below the critical temperature(normally working temperature below 77K) is direct current (DC) biased just below the critical current.

(ii) When a photon is absorbed by the nanowire creating a small resistive hotspot. (iii) The supercurrent is forced to flow along the periphery of the hotspot. Since the superconducting nanowires are narrow, the local current density around the hotspot increases, exceeding the superconducting critical current density.

(iv) This in turn leads to the formation of a resistive barrier across the width of the nanowire .

(v) Joule heating (via the DC bias) aids the growth of resistive region along the axis of the nanowire until the current flow is blocked and the bias current is shunted by the external circuit.

(vi) This allows the resistive region to subside and the wire becomes fully superconducting again. The bias current through the nanowire returns to the original value.


(b) A simple electrical equivalent circuit of a SNSPD.

Lk is the kinetic inductance of the superconducting nanowire and Rn is the hotspot resistance of the SNSPD.


The SNSPD is current biased at Ibias. Opening and closing the switch simulates the absorption of a photon. An output pulse is measured across the load resistor.

(c) A simulation of the output voltage pulse of the SNSPD (approximating the pulse shape typically observed on an oscilloscope after amplification). Values of Lk and Rn have been used for this simulation (for simplicity the Rn is assumed fixed, although a more detailed treatment. The solid blue line is the leading edge of the SNSPD output pulse, whilst the dotted red line is the trailing edge of the output pulse. The time constants relate to the phases of the detection cycle.


Applications




Optical Quantum Computation




Quantum Light Source Characterization




Quantum Communication



Laser Communication



Biological Fluorescence Detection





Non-Destructive Chip Testing

Specification

Parameters		Typical [*]	Optimum
	1550 nm	≥70%	≥90%
	1064 nm	≥70%	≥80%
Detection	850 nm	≥70%	≥80%
Efficiency	532 nm	≥70%	≥80%
Dark count rate		≤100 Hz	≤1 Hz
Timing jitter		40-70 ps	≤20 ps
Counting rate		≥20 MHz	≥100 MHz
Working Temperature		77 K	
Dimension		320 mm(D) X 245 mm(W) X 195 mm (H)	
Weight		5.0 Kg	
*① All the resulsts were tested at 77K; ② Customerization is available.			

SDE and DCR Curve





CA OPTRONICS GROUP INC. 3652 Edison Way, Fremont, CA 94538, USA Tel: (510 DOC No; 61000101 V1.02


Tel: (510)-366-7353

Fax: (510)-353-1809 http://www.caoptronicsgroup.com

532 nm

Outline Look





Liability Note:

This document is sole property of CA OPTRONICS GROUP INC. No part of this document may be copied without written acceptance of CA OPTRONICS GROUP INC. All statements related to the products herein are believed to be reliable and accurate. However, the accuracy is not guaranteed and no responsibility is assumed for any inaccuracies. CA OPTRONICS GROUP INC. reserves the right to make changes in the specifications at any time without prior notice.